

Note: We are enhancing our systems and you may notice duplicate entries/missing/outdated data. During this interim period, please contact our Customer Service at <https://www.ul.com/about/locations>.


Motor Controllers, Float- and Pressure-operated Certified for Canada - Component

COMPANY

CKD Corporation

1-850 Horinouchi-Cho-Kita
Kasugai-Shi, Aichi 486-8530 Japan

E492795

Marking: Company name model designation, and the Recognized Component Mark for Canada 

Note: For additional marking information, refer to the [Guide Information Page](#).

Open type, Digital pressure switch, Model(s): PPG-D followed by -R, -P, or -V, followed by NV, NA, NC, PV, PA or PC, followed by -6BM, -6NM, or -6GM, or -6B, -6N, or -6G, followed by blank, 1, 2, or 3.

Last Updated on 2024-04-17

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."