

Note: We are enhancing our systems and you may notice duplicate entries/missing/outdated data. During this interim period, please contact our Customer Service at <https://www.ul.com/about/locations>.

Servo and Stepper Motors Certified for Canada - Component


COMPANY

CKD Corporation

2-250 OUJI

KOMAKI-SHI, Aichi 485-8551 Japan

E328765

Marking: Company name model designation, and the Recognized Component Mark for Canada 

Note: For additional marking information, refer to the [Guide Information Page](#).

Model(s): AX1R-022(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX1R-045(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX1R-075(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX1R-150(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX1R-210(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX2R-006(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX2R-012(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX2R-018(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX4R-009(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX4R-022(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX4R-045(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX4R-075(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes -P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX4R-10W(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes - P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX4R-150(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes - P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX4R-300(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes - P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

Model(s): AX4R-500(a)-(b)(C)(d)(f) "(a)" denotes N, D or M, "(b)" denotes NN or BS or BM, "(c)" denotes NN or EB, "(d)" denotes - P0, -P1, -P2 or blank, "(f)" denotes Blank, -V01, -V02, -V03, -V04, -V05, -V06, -V07 or -V08.

AX1 Series, Model(s): AX1022T (a), AX1045T (a), AX1075T (a), AX1150T (a), AX1210T (a)

AX2 Series, Model(s): AX2006T (b), AX2012T (b), AX2018T (b)

AX4 Series, Model(s): AX4022T (c), AX4045T (c), AX4075T (c), AX410WT (d), AX4150T (c), AX4300T (c), AX4500T (d)

AX4 Series, Model(s): AX4009T, followed by -(d)-(e), where (d) denotes P1, P2, P3 or blank and (e) denotes S, M or blank.

(a) - Followed by -(a)-(b)-(d)-(f), where (a) denotes B, BS or blank, (b) denotes C or blank, (d) denotes P1, P2, P3 or blank, (f) denotes V01, V02, V03, V04, V05, V06, V07 or V08.

(b) - Followed by -(a)-(d)-(e), where (a) denotes B, BS or blank, (d) denotes P1, P2, P3 or blank and (e) denotes S, M or blank.

(c) - Followed by -(a)-(c)-(d)-(e)-(f), where (a) denotes B, BS or blank, (c) denotes EB or blank, (d) denotes P1, P2, P3 or blank, (e) denotes S, M or blank, and (f) denotes V01, V02, V03, V04, V05, V06, V07 or V08.

(d) - Followed by -(a)-(d)-(e)-(f), where (a) denotes B, BS or blank, (d) denotes P1, P2, P3 or blank, (e) denotes S, M or blank, and (f) denotes V01, V02, V03, V04, V05, V06, V07 or V08.

Last Updated on 2024-01-16

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."